## Capacitance and Dissipation Factor Measuring Bridge Type TG-1MOD



- For high voltage insulations diagnostics
- Allows precise measurements of capacitance and dissipation factor
- Measures impedances in all four quadrants
- Features classical balancing using analogue zero indicator and
- Fully automatic balancing
- Remote control and data transfer via RS232 interface
- Options: higher Cx current range

## **Prescoag**

Zürcherstrasse 70 CH – 8104 Weiningen Switzerland

Tel.: +41 44 750 63 63 Fax: +41 44 750 63 66 info@prescoag.com www.prescoag.com



## **Technical Specifications**

## **Capacitance and Dissipation Factor Measuring Bridge**

**Type TG-1MOD** 

Maximal current through test object 5 A (with range extension up to 20 A)

Maximal current through standard capacitor 30 mA

Capacitance measuring range  $0.1 \times C_N \dots 1'000 \times C_N$ 

(with range extension up to  $10'000 \times C_N$ )

Dissipation factor range  $1 \times 10^{-5} \dots 1$ 

Resolution dissipation factor 10<sup>-5</sup> (trough software 10<sup>-7</sup>)

Voltage measurement 10 V ... 1 MV Uncertainty of capacitance measurement  $\pm 0.01 \%$ 

Uncertainty of phase measurement ± 0.02 mrad ± 1 % of the displayed value

Uncertainty of voltage measurement ± 1 % of reading Measurement frequency 45 ... 65 Hz Interface RS232

**Display** 

capacitance display 6 decimals LED dissipation factor display 5 decimals LED voltage display 4 decimals LED  $C_N$  - setting 0.10 pF - 9999.99 pF

**Reference conditions** 

 $\begin{array}{ll} \mbox{Minimal current through standard capacitor} & 35 \ \mu\mbox{A} \\ \mbox{Temperature} & 23^{\circ}\mbox{C} \pm 2^{\circ}\mbox{C} \\ \mbox{Humidity} & 45 \dots 75 \ \% \\ \mbox{Air pressure} & 101.3 \ k\mbox{Pa} \\ \end{array}$ 

Rated range of use

according to IEC 359

Temperature 5°C ... 40°C Humidity, not condensing 20 ... 95 % Air pressure 70 ... 106 kPa

Dimension  $500 \times 470 \times 192 \text{ (w} \times d \times h \text{ in mm)}$ 

Weight 15kg

Power mains 230V / 50Hz / 25VA

automatic balancing by built-in computer

initial balancing 3 ... 5 seconds subsequent balancing 0.6 seconds

Every 2 minutes the initial balancing is restarted to compensate for possible instabilities in the convergence procedure caused for example by changes in frequency.

Option

Software for displaying and data processing

Type TG-0MOD-CP01

this software is compatible with Windows

functions:

processing the measurements displaying the measurements printing saving transfer to Excel data transfer by RS232 interface